

Datasheet

Item No. 70.350.1635.2

Hood BAS GOT GA 16 M25 50 A2

revos BASIC 500V size 16 hood with intermediate support M25, lateral cable entry, double locking lever



Item No.	70.350.1635.2
EAN	4015573598706
order unit	1 Piece(s)

Approvals



Technical data

General

Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	16
Model	Plug
Locking mechanism	Double locking levers
Cable entry	Sideways
Type of cable	Intermediate support
With cable screw gland	No
Thread size M	25
Hinged lid	No
EMC-version	No

Drawings

Ausführung .0
version .0

Kabelverschraubung M25
cable gland M25

Teile-Nr. part no.	Typ type
70.350.1635.0	BAS GOT GA 16 M25 50 A0
70.350.1635.1	BAS GOT GA 16 M25 50 A1
70.350.1635.2	BAS GOT GA 16 M25 50 A2
70.350.1635.3	BAS GOT GA 16 M25 50 A3
70.350.1635.4	BAS GOT GA 16 M25 50 A4
70.350.1635.5	BAS GOT GA 16 M25 50 A5

<p>Gewinde M25 thread M25</p> <p>Ausführung .1 version .1</p>	<p>Kabeldurchführung M25 mit Zugentlastung und Biegeschutz cable gland M25 with strain relief and bending protection</p> <p>Ausführung .3 version .3</p>	<p>Kabelverschraubung M25 mit Zugentlastung und Knickschutz cable gland M25 with strain relief and kink protection</p> <p>Ausführung .4 version .4</p>	<p>Stützen M25 intermediate support with thread M25</p> <p>Ausführung .2 version .2</p>
---	--	--	---

Freirolenanz nach -	MSBstab	Material und Oberfläche: Farbe: silbergrau colour: silvergrey	2003	Tag	Name	1. Vorwandlung: -	Bl: 1	von 1	Index
	x		09.07.			T	70.350.1635.0 01K		
	col.	mm	mm	mm	mm	Ersatz für: -			
						GEHAUSEOBERTEILE Größe 16 M25 schmale Seite H000 size 16 M25 narrow side			

A
1
2
3
4
5
6
7
8
9
10
11
12
13
14
15
16
17
18
19
20
M1
M2
M3
L
G
1
1.1
2.1
1.1

70.350.1635.01K_4 CADW20 Blatt 2/3 23.07.2003 08:10:28 1/000