

Datasheet

Item No. 70.353.0635.2

Hood BAS GOT GG 6 M25 50 A2

revos BASIC 500V size 6 hood with intermediate support M25, lateral cable entry, single locking lever



Item No.	70.353.0635.2
EAN	4015573651821
order unit	1 Piece(s)

Approvals



Technical data

General

Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	6
Model	Plug
Locking mechanism	Single locking lever
Cable entry	Sideways
Type of cable	Intermediate support
With cable screw gland	No
Thread size M	25
Hinged lid	No
EMC-version	No



Drawings

1
A
B
C
D
E
F

**Ausführung .1
version .1**

2
3
4
5
6

**Kabelverschraubung M25
cable gland M25**
Ausführung .0
version .0

Teile - Nr. part no.	Typ type
70.353.0635.0	BAS GOT GA 6 M25 50 A0
70.353.0635.1	BAS GOT GA 6 M25 50 A1
70.353.0635.2	BAS GOT GA 6 M25 50 A2
70.353.0635.3	BAS GOT GA 6 M25 50 A3
70.353.0635.4	BAS GOT GA 6 M25 50 A4
70.353.0635.5	BAS GOT GA 6 M25 50 A5

Weitere Daten siehe Katalog
further data see catalog

<p>Gewinde M25 thread M25 Ausführung .1 version .1</p>	<p>Kabeldurchführung M 25 mit Zugentlastung und Biegeschutz cable gland M25 with strain relief and bending protection Ausführung .3 version .3</p>	<p>Kabelverschraubung M25 mit Zugentlastung und Knickschutz cable gland M25 with strain relief on kink protection Ausführung .4 version .4</p>	<p>Kabelverschraubung M25 cable gland M25 Ausführung .5 version .5</p>
---	---	---	---

<p>Stützen M25 intermediate support with thread M25 Ausführung .2 version .2</p>			
---	--	--	--

IP 65

<p>Werkstoff/Material: 2006 Anfertiger/Date: 07.06. Treusch Zeichnung Nr./Drawing No. T 70.353.0635.0 01K</p>	
<p>GEHÄUSEOBERTEIL Größe 6/M25 schmale Seite Hood size 6/M25 narrow side</p>	