

## Datasheet

Item No. 72.350.0635.0

Hood BAS GOT GG 6 M20 69 A0

revos BASIC 690V size 6 hood with cable gland M20, lateral cable entry, single locking lever



Item No.	72.350.0635.0
EAN	4015573618312
order unit	1 Piece(s)

### Approvals



### Technical data

#### General

Nominal voltage	690
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	IP54
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

#### Model

DIN-size	6
Model	Plug
Locking mechanism	Single locking lever
Cable entry	Sideways
Type of cable	Gland nut
With cable screw gland	Yes
Thread size M	20
Hinged lid	No
EMC-version	No