

## Datasheet

Item No. 73.330.0635.1

Bottom BAS GUT GL 6HM25 69 A1

revos BASIC 500V size 6H closed-bottom base with 2 threaded collars M25, high design, single locking lever



Item No.	73.330.0635.1
EAN	4015573763272
order unit	1 Piece(s)

## Approvals



## Technical data

### General

Nominal voltage	690
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

### Model

DIN-size	6H
Model	Surface mounting (base)
Locking mechanism	Single locking lever
Cable entry	Two-sided
Type of cable	Thread
With cable screw gland	No
Thread size M	25
Hinged lid	No
EMC-version	No

Drawings

**Ausführung .1**  
**version .1**

Gewinde M25  
thread M25

**Gezeichnete Ausführung .0 / version .0**

66,7  
72,2  
6  
ca. 74,4

58  
4,5  
2,7  
4,4  
70  
84

Verschraubung M25  
screw connection M25

weitere Daten siehe Katalog  
further data see catalog

Teile-Nr. part-no.	Type
73.330.0635.0	BAS GUT GL 6HM25 69 A0
73.330.0635.1	BAS GUT GL 6HM25 69 A1

Freitoleranz nach -	Maßstab	Werkstoff und Oberfläche	CAD - Zeichnung, keine manuellen Änderungen	1. Verwendung: -	Bl. 1 von 1	Index
/	x		2004 Tag	Zeichnung Nr.		
/			Erweitert 11.08.	Kurz H.		
/			Gepolzt			
/	sol.	mm <sup>2</sup> Dtl.	mm <sup>2</sup> Nennquers.		Erstelle für: -	
a	09.06.2007			<b>GEHAUSEUNTERTEIL</b> housing lower part Größe/size 6 2x M25		
Änderung		Elektrische Verbindungen				

73330063501\_01\_200607.dwg 2006-06-09 10:11:06:30 1:1000