

## Datasheet

Item No. 73.350.4035.1

Hood BAS GOT GA 40HM25 50 A1

revos BASIC 500V size 16H hood with threaded collar M25, lateral cable entry, high design, double locking lever



Item No.	73.350.4035.1
EAN	4015573623590
order unit	1 Piece(s)

## Approvals



## Technical data

### General

Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

### Model

DIN-size	16H
Model	Plug
Locking mechanism	Double locking levers
Cable entry	Sideways
Type of cable	Thread
With cable screw gland	No
Thread size M	25
Hinged lid	No
EMC-version	No

Drawings

Wieland

Verschlusschraube M25  
cable gland M25

93,5  
47  
76  
43  
56  
6,5 ±0,2

Ausführung .0  
version .0

Weitere Daten siehe Katalog  
further data see catalog

Teile-Nr. part-number	Typ type
73.350.4035.0	BAS GOT GA 40 HM25 50 A0
73.350.4035.1	BAS GOT GA 40 HM25 50 A1
73.350.4035.2	BAS GOT GA 40 HM25 50 A2
73.350.4035.3	BAS GOT GA 40 HM25 50 A3
73.350.4035.4	BAS GOT GA 40 HM25 50 A4
73.350.4035.5	BAS GOT GA 40 HM25 50 A5

<b>Ausführung .1</b> version .1	<b>Ausführung .3</b> version .3	<b>Ausführung .5</b> version .5
<b>Ausführung .2</b> version .2	<b>Ausführung .4</b> version .4	

IP 65

Freitoleranz nach DIN	Maßstab	Werkstoff und Oberfläche	CAD - Zeichnung, keine manuellen Änderungen	2005	Tag	Monat	Zeichnung Nr.	Bl. 1	von 1	Index
	1:1			Erweitert	23.02.	Schnitt 1.	73.350.4035.0 01K			
				Geprüft						
				Nenngr.			Ersatz für:			
				Benennung		GEHÄUSEOBERTEIL Größe 40 M25 schmale Seite Hohl size 40 M25 narrow side				

73350403501L 2005-02-26T03:11:1000