

## Datasheet

Item No. 76.322.0760.5

Bottom MIN GUT GC 7 M20 25 P5

revos MINI size 3 closed-bottom base with cable gland M20, single locking lever, plastic housing



Item No.	76.322.0760.5
EAN	4015573782181
order unit	10 Piece(s)

## Technical data

### General

Nominal voltage	250
Housing material	Plastic
Colour	White
Surface	Untreated
Degree of protection (IP)	IP65
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	V0
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

### Model

DIN-size	3
Model	Surface mounting (base)
Locking mechanism	Single locking lever
Cable entry	Below
Type of cable	Gland nut
With cable screw gland	Yes
Thread size M	20
Hinged lid	No
EMC-version	No

Drawings

Material: PA666 GF30 Brandverh.UL94-V0

Freitoleranz nach DIN -		CAD - Zeichnung, keine manuellen Änderungen			1. Verwendung: -		Bl.: 1 von 1	
Maßstab		2004	Tag	Name		Zeichnung Nr.		Index
<b>x</b>		Entworfen	14.05.	Treschan		76.322.0760.5 01K		
		Gepüßt	-	-		Ersatz für: -		
		Normgepr.	-	-				
 <b>wieland</b> Elektrische Verbindungen				Benennung <b>GEHAEUSEUNTERTEIL</b> IP68 - Verschraubung M 20 7 - polig				
Buchstabe	Datum / Blatt							
Änderung								

A  
1  
2  
3  
4  
5  
6  
7  
8  
9  
10  
11  
12  
13  
14  
15  
16  
17  
18  
19  
20  
M1  
M2  
M3  
L  
G  
i  
1.1  
12.1  
1.1

763220760501K\_4\_CADW28\_Treschan 2004-05-17 11:35:40 1:000