

Datasheet

Item No. 76.353.1035.0

Hood BAS GOT GG 10HM32 50 A0

revos BASIC 500V size 10H hood with cable gland M32, lateral cable entry, high design, single locking lever



Item No.	76.353.1035.0
EAN	4015573687042
order unit	1 Piece(s)

Approvals



Technical data

General

Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	IP54
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	10H
Model	Plug
Locking mechanism	Single locking lever
Cable entry	Sideways
Type of cable	Gland nut
With cable screw gland	Yes
Thread size M	32
Hinged lid	No
EMC-version	No