

## Datasheet

Item No. 77.341.1635.0

Bottom BAS GUT GS 16 M25 69 A0

revos BASIC 690V size 16 closed-bottom base with cable gland M25, left, with cover, single locking lever



|            |               |
|------------|---------------|
| Item No.   | 77.341.1635.0 |
| EAN        | 4015573626768 |
| order unit | 1 Piece(s)    |

## Approvals



## Technical data

### General

|  |                     |
|--|---------------------|
| Nominal voltage  | 690                 |
| Housing material   | Aluminium           |
| Colour   | Grey                |
| Surface  | With powder coating |
| Degree of protection (IP)                                  | IP54                |
| UV resistant   | Yes                 |
| Inflammability class of insulation material acc. with UL94 | Other               |
| Operating temperature range min.                           | -40 °C              |
| Operating temperature range max.                           | 120 °C              |

### Model

|                        |                         |
|------------------------|-------------------------|
| DIN-size               | 16                      |
| Model                  | Surface mounting (base) |
| Locking mechanism      | Single locking lever    |
| Cable entry            | Sideways                |
| Type of cable          | Gland nut               |
| With cable screw gland | Yes                     |
| Thread size M          | 25                      |
| Hinged lid             | Yes                     |
| EMC-version            | No                      |

Drawings

Weitere Daten siehe Katalog  
further data see catalog

| Teilenummer<br>part-number | Typ<br>type             |
|----------------------------|-------------------------|
| 77.341.1635.0              | BAS GUT GS 16 M25 69 A0 |
| 77.341.1635.1              | BAS GUT GS 16 M25 69 A1 |

|                     |         |   |   |  |                 |              |  |                     |  |
|---------------------|---------|---|---|--|-----------------|--------------|--|---------------------|--|
| Freitoleranz nach - |         | CAD - Zeichnung, keine manuellen Änderungen |   | 1. Verwendung: -   |                 | Bl.: 1 von 1 |  | Index               |  |
| /                   | Maßstab | Merkstoff und Oberfläche:                   |   | 2005   | Tag             | Name         |  | Zeichnung Nr.       |  |
| /                   | 1:1     |   |   | Erweitert  | 31.02.          | Schnitt 1.   |  | T 77.341.1635.0 01K |  |
| /                   |         |   |   | Gepulvt  |                 |              |  | Ersatz für: -       |  |
| /                   | Vol.    | mm <sup>3</sup>                             | g | mm <sup>2</sup>  | mm <sup>2</sup> | Nennspann. - |  |                     |  |
|                     |         | <b>TYP</b><br>BAS GUT GS<br>16 M25 69       |   | Benennung<br><b>GEHÄUSEUNTERTEIL</b><br>und Schutzdeckel Größe 16 M 25 1xlinks<br>Closed housing w.cable gland left/protective cover |                 |              |  |                     |  |
| Änderung            |         | Elektrische Verbindungen                    |   |  |                 |              |  |                     |  |

A  
1  
2  
3  
4  
5  
6  
7  
8  
9  
10  
11  
12  
13  
14  
15  
16  
17  
18  
19  
20  
M1  
M2  
M3  
L  
G  
1  
1.1  
1.1.1  
1.1.1.1  
773411635001\_1\_2006028\_Schnitt\_2005-02-27T11:22:49\_1000