

## Datasheet

Art.No. 92.042.9658.1

### Male connector GST18i4F S2 R V SW

Device connectors, snap-in panel mount, GST18i4, 4 pole, male, spring clamp connection, 250/400 V, 20 A, material thickness 0,5 - 1,5 mm, colour of coding: black



Art.No.	92.042.9658.1
EAN	4015573399587
Order unit	100 pieces

## Approvals



## Technical data

### General

Rated current	20 A
Rated voltage	400 V
Pollution degree	2
Mechanical coding	Code 1
Rated impulse voltage	4 kV
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	

### Connection Data

Connection cross section solid	2.5 mm <sup>2</sup>
Cross section solid 2	0.5 mm <sup>2</sup>
Connection cross section stranded	1.5 mm <sup>2</sup>
Cross section stranded 2	0.5 mm <sup>2</sup>
Terminations per pole	2

### Model

Model	male
Number of poles	4
Connection type	Tension clamp connection
Connecting thread metric	No thread
Angle of plug	Straight
Degree of protection (IP)	IP40

Remark to type of connection	Finely stranded con. req. Wieland cable end sleeve
Thickness of housings (electrical device) 2	0.5 mm
Thickness of housings (electrical device)	1.5 mm
Built-in component	Snap-in

### Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Tin-plated

### Dimensions

Length	38 mm
Width	42.5 mm
Height	18.5 mm

