

Datasheet

Item No. 93.431.2353.1

Female connector BST14I3F B1 R SW

Device connectors, snap-in panel mount, BST14i3, 4 pole, female, spring clamp connection, 50V/3A, color of coding: black, color of frame: black



Item No.	93.431.2353.1
EAN	4015573492189
order unit	100 Piece(s)

Approvals



Technical data

General

Rated current	3 A
Rated voltage	50 V
Pollution degree	2
Mechanical coding	Yes
Rated impulse voltage	0.8 kV
Interlockable	Yes
Color of coding/ contact carrier	Black
Connection cross section solid	0.75 mm ²
Cross section solid 2	0.5 mm ²
Connection cross section stranded	0.75 mm ²
Cross section stranded 2	0.5 mm ²
Terminations per pole	1

Model

Model	Bus
Number of poles	3
Connection type	Tension clamp connection
Angle of plug	Straight
Degree of protection (IP)	IP20
Thickness of housings (electrical device) 2	0.5 mm
Thickness of housings (electrical device)	1.5 mm
Built-in component	Snap-in/screw-in

Material

Housing material	Polyamide
------------------	-----------

Contact material	Other
Insulation components continuous temperature	100 °C
Surface finish	Gilt

Dimensions

Length	29.9 mm
Width	19.6 mm
Height	19.6 mm