

Datasheet

Item No. 96.020.0253.1

Distributor RST20I2V 3P1 F V SW

Distribution block RST20i2, 2 pole, 1 input, 3 outputs, without mounting option, 250V/20A, color of coding: black



Item No.	96.020.0253.1
EAN	4015573949577
order unit	100 Piece(s)

Approvals



Technical data

General

Rated current	20 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Black

Model

Number of poles	2
Number of inputs	1
Number of outputs	3
Type of fastening	No
Degree of protection (IP)	IP66/IP68
Type of distributor	Distribution terminal block

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	55.5 mm
--------	---------

Width	69.6 mm
Height	31.3 mm

Drawings

Gezeichnete Ausführung 96.020.0153.F
drawn construction: 96.030.0153.0

Ausführung: 96.020.0253.F
Variante ohne Anschraubflansch
drawn construction: 96.020.0253.F
variante: without screwing flange
M1:1

Ausführung: 96.020.0153.F
Variante mit Anschraubflansch
drawn construction: 96.020.0253.F
variante: with screwing flange
M1:1

Teil-Nr. part-no.	Typ typ	Farbe color	Variante variante
96.020.0153.1	RST2012V-3P1-F-V-GR	schwarz, ähnlich RAL 9005	mit Anschraubflansch
96.020.0153.2	RST2012V-3P1-F-V-GR	grau, ähnlich RAL 9005	mit Anschraubflansch
96.020.0153.3	RST2012V-3P1-F-V-GR	grau, ähnlich RAL 7032	mit Anschraubflansch
96.020.0253.1	RST2012V-3P1-V-SW	schwarz, ähnlich RAL 9005	ohne Anschraubflansch
96.020.0253.2	RST2012V-3P1-V-SW	grau, ähnlich RAL 9005	ohne Anschraubflansch
96.020.0253.3	RST2012V-3P1-V-GR	grau, ähnlich RAL 7032	ohne Anschraubflansch

96.020.0153.0 01K a

VERTEILER