

## Datasheet

Item No. 96.021.0153.1

### Female connector with strain relief RST20I2F B23ZR2 S

Connector RST20I2, 2 pole, female, spring clamp connection, 250V/20A, for cable diameters 10-14 mm, color of coding: black, color of housing: black



Item No.	96.021.0153.1
EAN	4015573904316
order unit	100 Piece(s)

### Approvals



### Technical data

#### General

Rated current	20 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pull relief	Yes
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Black

#### Connection Data

Cable diameter	10 mm
Connection cross section solid	2.5 mm <sup>2</sup>
Connection cross section stranded	1.5 mm <sup>2</sup>
Terminations per pole	2

#### Model

Model	Bus
Number of poles	2
Connection type	Tension clamp connection
Degree of protection (IP)	IP66/IP68
Remark to type of connection	Finely stranded con. req. Wieland cable end sleeve

#### Material

Housing material	Polyamide
Halogen free	Yes

