

## Datasheet

Item No. 96.021.4053.0

### Female connector with strain relief RST20I2S B13ZR1 G

Connector RST20i2, 2 pole, female, screw connection, 250V/20A, for cable diameters 6-10 mm, color of coding: light gray, color of housing: light gray



Item No.	96.021.4053.0
EAN	4015573852372
order unit	100 Piece(s)

### Approvals



### Technical data

#### General

Rated current	20 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pull relief	Yes
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Light grey

#### Connection Data

Cable diameter	6 mm
Connection cross section solid	4 mm <sup>2</sup>
Connection cross section stranded	4 mm <sup>2</sup>
Terminations per pole	1

#### Model

Model	Bus
Number of poles	2
Connection type	Screw connection
Degree of protection (IP)	IP66/IP68

#### Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn

