

Datasheet

Item No. 96.022.0053.1

Male connector with strain relief RST20I2F S23ZR1 V S'

Connector RST20I2, 2 pole, male, spring clamp connection, 250V/20A, for cable diameters 6-10 mm, color of coding: black, color of housing: black



Item No.	96.022.0053.1
EAN	4015573890510
order unit	100 Piece(s)

Approvals



Technical data

General

Rated current	20 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pull relief	Yes
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Black

Connection Data

Connection cross section solid	2.5 mm ²
Connection cross section stranded	1.5 mm ²
Terminations per pole	2

Model

Model	Plug
Number of poles	2
Connection type	Tension clamp connection
Degree of protection (IP)	IP66/IP68
Remark to type of connection	Finely stranded con. req. Wieland cable end sleeve

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn

