

Datasheet

Item No. 96.022.4050.8

Male connector with strain relief RST20I2S S13ZR1SVL

Connector RST20I2, 2 pole, male, screw connection, 50V/20A, for cable diameters 6-10 mm, color of coding: pebble gray, color of housing: black



Item No.	96.022.4050.8
EAN	4015573956353
order unit	100 Piece(s)

Approvals



Technical data

General

Rated current	20 A
Rated voltage	24 V
Rated impulse voltage	4 kV
Pull relief	Yes
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Pebble gray

Connection Data

Connection cross section solid	4 mm ²
Connection cross section stranded	4 mm ²
Terminations per pole	1

Model

Model	Plug
Number of poles	2
Connection type	Screw connection
Degree of protection (IP)	IP66/IP68

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C

