

Datasheet

Art.No. 96.041.4053.0

Female connector with strain relief RST20i4S B1 ZR1 GL

Connector RST20i4, 4 pole, female, screw connection, 250/400V, 20A, for cable diameters 6-10 mm, color of coding: light gray, color of housing: light gray



Art.No.	96.041.4053.0
EAN	4015573863095
Order unit	100 pieces

Approvals



Technical data

General

Rated current	20 A
Rated voltage	400 V
Rated impulse voltage	4 kV
Pull relief	Yes
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Light grey
Marking of poles	

Connection Data

Connection cross section solid	4 mm ²
Connection cross section stranded	4 mm ²
Terminations per pole	1

Model

Model	female
Number of poles	4
Connection type	Screw connection
Degree of protection (IP)	IP66/IP68

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	80.4 mm
Width	34.6 mm
Height	34.6 mm

