

Datasheet

Item No. 96.041.6053.1

Female connector RST20I4S B1 M00 SW

Device connectors, modular M20, RST20i4, 4 pole, straight, female, screw connection, 250/400V, 20A, color of coding: black, color of housing: black



Item No.	96.041.6053.1
EAN	4015573863248
order unit	100 Piece(s)

Approvals



Technical data

General

Rated current	20 A
Rated voltage	400 V
Pollution degree	3
Mechanical coding	Yes
Rated impulse voltage	4 kV
Interlockable	Yes
Color of coding/ contact carrier	Black
Color of separate adapter (if present)	Black
Connection cross section solid	4 mm ²
Connection cross section stranded	4 mm ²
Terminations per pole	1

Model

Model	Bus
Number of poles	4
Connection type	Screw connection
Connecting thread metric	M20
Angle of plug	Straight
Degree of protection (IP)	IP66/IP68
Built-in component	Snap-in/screw-in

Material

Housing material	Polyamide
Halogen free	Yes

