

Datasheet

Art.No. 96.051.5053.6

Female connector RST20i5S B1 M01 A TB04

Device connectors, standard M25, RST20i5, 5 pole, female, screw connection, mains 250V/dimming, 20A, color of coding: turquoise, color of nut: black



Art.No.	96.051.5053.6
EAN	4015573877542
Order unit	100 pieces

Approvals



Technical data

General

Rated current	20 A
Rated voltage	250 V
Rated voltage 2	50 V
Pollution degree	3
Mechanical coding	Yes
Rated impulse voltage	4 kV
Interlockable	Yes
Color of coding/ contact carrier	Turquoise
Marking of poles	

Connection Data

Connection cross section solid	4 mm ²
Connection cross section stranded	4 mm ²
Terminations per pole	1

Model

Model	female
Number of poles	5
Connection type	Screw connection
Connecting thread metric	M25
Angle of plug	Straight
Degree of protection (IP)	IP66/IP68
Built-in component	Snap-in/screw-in

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	51.3 mm
Width	35 mm
Height	35 mm

Drawings

