

Datasheet

Art.No. 92.032.0058.1

Male connector GST18i3L S1V SW

Device connectors, PCB mount, GST18i3, 3 pole, vertical, male, 250 V, 20 A, colour of coding: black



Art.No.	92.032.0058.1
EAN	4015573454552
Order unit	1 pieces

Approvals



Technical data

General

Rated current	20 A
Rated voltage	250 V
Pollution degree	2
Mechanical coding	Code 1
Rated impulse voltage	4 kV
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	

Connection Data

Terminations per pole	1
-----------------------	---

Model

Model	male
Number of poles	3
Connection type	Soldering connection
Connecting thread metric	No thread
Angle of plug	Straight
Degree of protection (IP)	IP20
Built-in component	Soldering connection

Material

Housing material	Polyamide
------------------	-----------

Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Tin-plated

Dimensions

Length	24 mm
Width	28.2 mm
Height	13 mm

Accessories

Art.No.:	Type:	Description
05.561.3653.0	Cover cap GST18I3VS B WS	Cover piece for female GST18i3, white
05.561.3653.1	Cover cap GST18I3VS B SW	Cover piece for female GST18i3, black
05.564.5353.0	Cover cap GST18I3/4/5 SW	Cover piece 12 pole for GST18i3-6
05.564.5353.2	Cover cap GST18I3/4/5 WS	
05.590.4556.0	Locking slide GST18 WS	Locking device for solder connections GST18i3-5, white
05.590.4556.1	Locking slide GST18 SW	Locking device for solder connections GST18i3-5, black
05.594.4250.0	Cover cap ST18/3B + GST18I3 ST WS	
05.594.4253.0	Cover cap ST18/3B + GST18I3 ST WS	

