

Search ... / article no. / type

Fast product entry

Excel product upload

- > Industrial multipole connection - revos
- > Bottom BAS GUT GI 40HM32 50 A1

← To overview



BOTTOM BAS GUT GI 40HM32 50 A1

Articlenr. **73.347.4035.1**

Bottom-base revos basic made of aluminum, with double locking lever and threaded hole M32 on the bottom, with protective cover, low version, 40-polig

Price

Stock 

Quantity

1

pieces



ADD TO CART

TECHNICAL DATA**DOWNLOADS****ACCESSORIES****FITS WITH****DATA SHEET**

Commercial data

Article number	73.347.4035.1
Article description	Bottom BAS GUT GI 40HM32 50 A1
EAN	4015573630017
Order Unit	1 piece(s)
Country of origin	DE
Customs tariff number	85369010

Dimensions

Length packed	470 mm
Width packed	160 mm
Height packed	0 mm
Gross weight packed	395 g
Net weight single part	385.1 g
Volume packed	520.2 ccm

FIND MORE INFORMATION ABOUT THIS PRODUCT IN **WIELAND ELECTRIC'S PRINT MEDIA** HERE.

TO CATALOG VIEW

Productfamilies

DIN Rail terminal blocks
Building installation systems
(IPX0) - gesis® PCB terminals -
wiecon Safety technology -
safety

Building automation - gesis®
electronic Industrial multipole
connection - revos Interface
technology Circular connector
system in raised degree of
protection (IP6X) - RST®

Industrial communication
Power bus system - podis
Others

Customer Login

 [Login](#)



Imprint **Terms and Conditions** **Data Privacy Statement**

© 2021 Wieland Electric GmbH. All rights reserved.



English