

Datasheet

Art.No. 02.125.5521.8

Female contact CRIMP RST20i4/i5 1,0QMM

RST20i5/4 crimp contact, female, 20A, for cross section 0.75-1.0 mm²/AWG17



Art.No.	02.125.5521.8
EAN	4015573865242
Order unit	100 pieces

Approvals

Technical data

Classification

ETIM 6.0	EC000796
----------	----------

Drawings

gezeichnete Ausführung / drawn version: 02.125.58XX.X

23,1

Teilschnitt A-A
partial cross section A-A

gezeichnete Ausführung: 02.125.57XX.X/
drawn version: 02.125.57XX.X

Kennzeichnungsstelle(n)
marking chamfer

Verpackungseinheit: 100 Stück pro Karton
packaging unit: per 100 per carton

02.125.5821.8	versilbert/ silver-plated	4,0 mm ²	- ohne - - without -	2,85 mm	3,9 mm
02.125.5802.0	silver-plated				
02.125.5721.8	versilbert/ silver-plated	2,5 mm ²	2 Rillen 2 chamfer	2,25 mm	3,45 mm
02.125.5702.0	silver-plated				
02.125.5621.8	versilbert/ silver-plated	1,5 mm ²	1 Rille 1 chamfer	1,75 mm	3,0 mm
02.125.5602.0	silver-plated				
02.125.5521.8	versilbert/ silver-plated	0,75-1 mm ²	- ohne - - without -	1,45 mm	2,6 mm
02.125.5502.0	silver-plated				
Teile-Nr. part-no.	Oberfläche surface	Anschluss- querschnitt connection cross-section	Kenn- zeichnung marking	Ød _i	ØD ₀

02.125.580001N_3 CA000330 Line 2015-06-15 15:09:36:08 1.000

BUCHSENKONTAKT RST2014/5

female contact

Wieland

Wieland Electric

02.125.580001N_3 CA000330 Line 2015-06-15 15:09:36:08 1.000