

Datasheet

Art.No. 73.330.4035.1

Bottom BAS GUT GB 40HM25 50 A1

revos BASIC 500V size 16H closed-bottom base with 2 threaded collars M25, high design, double locking lever



Art.No.	73.330.4035.1
EAN	4015573621985
Order unit	1 pieces

Approvals



Technical data

General

Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	16H
Model	Surface mounting (base)
Locking mechanism	Double locking levers
Cable entry	Two-sided
Type of cable	Thread
With cable screw gland	No
Thread size M	25
Hinged lid	No
EMC-version	No