

Datasheet

Art.No. 76.350.1535.2

Hood HD GOT GG 15 M20 50 A2

revos HD size 10/15 hood with intermediate support M20, lateral cable entry, single locking lever



Art.No.	76.350.1535.2
EAN	4015573625792
Order unit	1 pieces

Approvals



Technical data

General

Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	10/15
Model	male
Locking mechanism	Single locking lever
Cable entry	Sideways
Type of cable	Intermediate support
With cable screw gland	No
Thread size M	20
Hinged lid	No
EMC-version	No

