

Datasheet

Art.No. 76.353.4035.2

Hood BAS GOT GG 40HM32 50 A2

revos BASIC 500V size 16H hood with intermediate support M32, lateral cable entry, high design, single locking lever



Art.No.	76.353.4035.2
EAN	4015573625020
Order unit	1 pieces

Approvals



Technical data

General

Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	16H
Model	male
Locking mechanism	Single locking lever
Cable entry	Sideways
Type of cable	Intermediate support
With cable screw gland	No
Thread size M	32
Hinged lid	No
EMC-version	No

