

Datasheet

Art.No. 81.020.0010.0

Timer relay flare TIME OFF-1

flare TIME OFF-1, OFF-delay timer relay without auxiliary supply, 2 time-ranges,
1 change-over contact, 1s - 120s, AC 200-240 V, 50-60Hz; W x H x D: 22,5 ×
89,4 × 100 mm



Art.No.	81.020.0010.0
EAN	4049088154829
Order unit	1 pieces

Approvals



Technical data

General

Connection type	Screw connection
Plug-in socket	No
Remote operation possible	No
Only for remote control	No
Function flashing, starting with pause, fixed time	No
Function flashing, starting with pulse, fixed time	No
Clock function, starting with pause, variable	No
Clock function, starting with pulse, variable	No
Number of relay outputs, undelayed, change-over contacts	0
Relay outputs, delayed/undelayed selectable	No
Number of relay outputs, undelayed, normally closed	0
Number of relay outputs, undelayed, normally open	0
Number of relay outputs, delayed, change-over contacts	0
Number of relay outputs, delayed, normally open	0
Number of relay outputs, delayed, change-over contacts	1
Semiconductor output	No
Function delay-on energization	No
Function floating contact on energization	No
Function star-delta	No
Function delay on de-energization	Yes
Function floating contact on de-energization	No
Function pulse shaping	No

Technical data

Type of excitation	
With auxiliary voltage	No
Min. rated AC voltage for controls, 50 Hz	170 V
Max. rated AC voltage for controls, 50 Hz	264 V
Min. rated AC voltage for controls, 60 Hz	170 V
Max. rated AC voltage for controls, 60 Hz	264 V
Min. rated frequency	50 Hz
Max. rated frequency	60 Hz
Min. adjustable time	0.1 sec
Max. adjustable time	10 sec

Dimensions

Depth	79 mm
Width	22.5 mm
Height	100 mm