

Datasheet

Art.No. 91.941.9053.0

Female connector GST15i4S B1 R V WS

Device connectors, snap-in panel mount, GST15i4, 4 pole, female, screw connection, 250/400V, 16A, material thickness 0,5 - 1,5 mm,color of coding: white, color of frame: white



Art.No.	91.941.9053.0
EAN	4015573934566
Order unit	1 pieces

Approvals



Technical data

General

Rated current	16 A
Rated voltage	400 V
Rated voltage 2	250 V
Pollution degree	2
Mechanical coding	Code 1
Rated impulse voltage	4 kV
Interlockable	Yes
Color of coding/ contact carrier	White
Marking of poles	
Color of separate adapter (if present)	White

Connection Data

Connection cross section solid	2.5 mm ²
Cross section solid 2	0.5 mm ²
Connection cross section stranded	2.5 mm ²
Cross section stranded 2	0.5 mm ²
Terminations per pole	1

Model

Model	female
Number of poles	4
Connection type	Screw connection
Connecting thread metric	M3

Angle of plug	Straight
Degree of protection (IP)	IP20
Thickness of housings (electrical device) 2	0.5 mm
Thickness of housings (electrical device)	1.5 mm
Built-in component	Snap-in/screw-in

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	31.2 mm
Width	34.6 mm
Height	19.6 mm

Drawings

