

Datasheet

Art.No. 91.952.4053.1

Male connector with strain relief GST15I5S S1 ZR1W SW



Art.No.	91.952.4053.1
EAN	4049088037832
Order unit	1 pieces

Approvals



Technical data

General

Rated current	16 A
Rated voltage	250 V
Rated voltage 2	250 V
Rated impulse voltage	4 kV
Strain relief	Yes
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	
Color of housing inclusive strain relief	Black

Connection Data

Cable diameter	12 mm
Cable diameter 2	7.5 mm
Connection cross section solid	2.5 mm ²
Cross section solid 2	0.5 mm ²
Connection cross section stranded	2.5 mm ²
Cross section stranded 2	0.5 mm ²
Terminations per pole	1

Model

Model	male
-------	------

Number of poles	5
Connection type	Screw connection
Degree of protection (IP)	IP20

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	78 mm
Width	32 mm
Height	15 mm

