

Datasheet

Art.No. 92.030.2153.0

Distributor GST18i3VN2P1 V WS

Direct luminaire connection (gesis TOP), GST18i3, 3 pole, 1 input, 1 output, 250 V, 20 A, 1 output for light internal lamp connector, re-tool of special prepared luminaires 2 A, colour of coding: white, colour of housing: white



Art.No.	92.030.2153.0
EAN	4015573893528
Order unit	1 pieces

Approvals



Technical data

General

Rated current	20 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	White
Marking of poles	

Model

Number of poles	3
Number of inputs	1
Number of outputs	2
Type of fastening	Yes
Degree of protection (IP)	IP20
Type of distributor	Integrated lamp connector

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	Other
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	59 mm
Width	30.4 mm
Height	29.55 mm

