

**Datasheet**

Art.No. 93.421.0553.1

Female connector with strain relief BST14i2F B1 ZR1 S MGN01

Connector BST14i2, 2 pole, female, spring clamp connection, 50V/3A, color of coding: green, color of housing: black



Art.No.	93.421.0553.1
EAN	4015573442542
Order unit	1 pieces

**Approvals**



**Technical data**

**General**

Rated current	3 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Strain relief	Yes
Pollution degree	2
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Green
Marking of poles	
Color of housing inclusive strain relief	Black

**Connection Data**

Cable diameter	6.5 mm
Cable diameter 2	5.5 mm
Terminations per pole	1

**Model**

Model	female
Number of poles	2
Connection type	Tension clamp connection
Degree of protection (IP)	IP20

**Material**

Housing material	Polyamide
Halogen free	Yes
Contact material	Other
Insulation components continuous temperature	100 °C
Surface finish	Gilt

**Dimensions**

Length	47 mm
Width	15.2 mm
Height	14.4 mm

Drawings

