

Datasheet

Art.No. 96.021.5050.8

Female connector RST20i2S B13 M01 L KG06

Device connectors, standard M25, RST20i2, 2 pole, female, screw connection, 50V/20A, color of coding: pebble gray, color of nut: black



Art.No.	96.021.5050.8
EAN	4015573955196
Order unit	1 pieces

Approvals

Technical data

General

Rated current	20 A
Rated voltage	24 V
Pollution degree	3
Mechanical coding	Yes
Rated impulse voltage	4 kV
Interlockable	Yes
Color of coding/ contact carrier	Pebble gray
Marking of poles	

Connection Data

Connection cross section solid	4 mm <sup>2</sup>
Connection cross section stranded	4 mm <sup>2</sup>
Terminations per pole	1

Model

Model	female
Number of poles	2
Connection type	Screw connection
Connecting thread metric	M25
Angle of plug	Straight
Degree of protection (IP)	IP66/68 (3m;2h) /IP69K
Built-in component	Snap-in/screw-in

Material

Housing material	Polyamide
------------------	-----------

Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

**Dimensions**

Length	46.5 mm
Width	35 mm
Height	35 mm

