

Datasheet

Art.No. 96.031.4155.7

Female connector with strain relief RST20i3S B1 ZR2SH GN02

Connector RST20i3, 3 pole, female, screw connection, 250V/20A, for cable diameters 10-14 mm, color of coding: green, color of housing: black



Art.No.	96.031.4155.7
EAN	4015573875142
Order unit	1 pieces

Approvals



Technical data

General

Rated current	20 A
Rated voltage	400 V
Rated impulse voltage	4 kV
Strain relief	Yes
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Green
Marking of poles	

Connection Data

Connection cross section solid	4 mm ²
Connection cross section stranded	4 mm ²
Terminations per pole	1

Model

Model	female
Number of poles	3
Connection type	Screw connection
Degree of protection (IP)	IP66/68 (3m;2h) /IP69K

Material

Housing material	Polyamide
------------------	-----------

Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	80.4 mm
Width	34.6 mm
Height	34.6 mm

