


Datasheet

Art.No. 96.032.4053.9

Male connector with strain relief RST20I3S S1 ZR1SV BL07

Connector RST20i3, 3 pole, male, screw connection, 250V/20A, for cable diameters 6-10 mm, color of coding: blue, color of housing: black



Art.No.	96.032.4053.9
EAN	4015573982703
Order unit	1 pieces

Approvals



Technical data

General

Rated current	20 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Strain relief	Yes
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Blue
Marking of poles	
Color of housing inclusive strain relief	Black

Connection Data

Cable diameter	10 mm
Cable diameter 2	6 mm
Connection cross section solid	4 mm ²
Cross section solid 2	0.75 mm ²
Connection cross section stranded	4 mm ²
Cross section stranded 2	0.75 mm ²
Terminations per pole	1

Model

Model	male
Number of poles	3

Connection type	Screw connection
Degree of protection (IP)	IP66/68 (3m;2h) /IP69K

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	78.4 mm
Width	34.6 mm
Height	34.6 mm

Drawings

