

Datasheet

Art.No. 96.032.6053.9

Male adapter RST20I3S S1 M00V BL07

Device connectors, modular M20, RST20I3, 3 pole, straight, male, screw connection, 250V/20A, color of coding: blue, color of housing : black



Art.No.	96.032.6053.9
EAN	4015573985117
Order unit	1 pieces

Approvals



Technical data

General

Rated current	20 A
Rated voltage	250 V
Pollution degree	3
Mechanical coding	Yes
Rated impulse voltage	4 kV
Interlockable	Yes
Color of coding/ contact carrier	Light blue
Marking of poles	
Color of separate adapter (if present)	Black

Connection Data

Connection cross section solid	4 mm ²
Cross section solid 2	0.75 mm ²
Connection cross section stranded	4 mm ²
Cross section stranded 2	0.75 mm ²
Terminations per pole	1

Model

Model	male
Number of poles	3
Connection type	Screw connection
Connecting thread metric	M20
Angle of plug	Straight

Inclination	0 °
Degree of protection (IP)	IP66/68 (3m;2h) /IP69K
Built-in component	Built-in component/connector

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	65.3 mm
Width	34.7 mm
Height	34.7 mm

