

Datasheet

Art.No. 96.033.4153.1

Female connector with strain relief RST20i3S B1 YR2 SW

Connector RST20i3, 3 pole, rectangular, female, screw connection, 250V/20A, for cable diameters 10-14 mm, color of coding: black, color of housing: black



Art.No.	96.033.4153.1
EAN	4049088000454
Order unit	1 pieces

Approvals



Technical data

General

Rated current	20 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Strain relief	Yes
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	
Color of housing inclusive strain relief	Black

Connection Data

Cable diameter	14 mm
Cable diameter 2	10 mm
Connection cross section solid	4 mm ²
Cross section solid 2	0.75 mm ²
Connection cross section stranded	4 mm ²
Cross section stranded 2	0.75 mm ²
Terminations per pole	1

Model

Model	female
Number of poles	3

Connection type	Screw connection
Degree of protection (IP)	IP66/68 (3m;2h) /IP69K

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	73.4 mm
Width	34.6 mm
Height	62.3 mm