

Datasheet

Art.No. 96.052.4053.6

Male connector with strain relief RST20I5S S1 ZR1SVA TB04

Connector RST20i5, 5 pole, male, screw connection, mains 250V/dimming, 20A, for cable diameters 6-10 mm, color of coding: turquoise, color of housing: black



Art.No.	96.052.4053.6
EAN	4015573877689
Order unit	1 pieces

Approvals



Technical data

General

Rated current	20 A
Rated voltage	250 V
Rated voltage 2	50 V
Rated impulse voltage	4 kV
Strain relief	Yes
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Turquoise
Marking of poles	
Color of housing inclusive strain relief	Black

Connection Data

Connection cross section solid	4 mm <sup>2</sup>
Connection cross section stranded	4 mm <sup>2</sup>
Terminations per pole	1

Model

Model	male
Number of poles	5
Connection type	Screw connection
Degree of protection (IP)	IP66/68 (3m;2h) /IP69K

**Material**

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

**Dimensions**

Length	80.4 mm
Width	34.6 mm
Height	34.6 mm

Drawings

**Auslieferungszustand**  
**delivery status**

for cable diameter 6-10mm  
for cable diameter 6-10mm  
color: black,  
similar to RAL 9005  
Farbe: schwarz,  
ähnl. RAL 9005

color: turquoise/blue,  
similar to RAL 5018  
Farbe: türkisblau,  
ähnl. RAL 5018

**Verpackungseinheit: je 100 Stück**  
**packaging unit: per 100**

**A-A**

**Type: RST2015S S1 ZR15VA TB04**

Steckerteile mit Zugentlastung  
Stecker mit Zugentlastung

96.052.4053.6 01K b

Wieland  
Mechanische Stecksteckungen