

## Datasheet

Art.No. 96.052.4151.4

Male connector with strain relief RST20I5S S1 ZR2SVL BR01

Connector RST20i5, 5 pole, male, screw connection, 50V, 20A, for cable diameters 10-14 mm, color of coding: brown, color of housing: black



Art.No.	96.052.4151.4
EAN	4015573891029
Order unit	1 pieces

## Approvals



## Technical data

### General

Rated current	20 A
Rated voltage	50 V
Rated impulse voltage	4 kV
Strain relief	Yes
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Brown
Marking of poles	

### Connection Data

Connection cross section solid	4 mm <sup>2</sup>
Connection cross section stranded	4 mm <sup>2</sup>
Terminations per pole	1

### Model

Model	male
Number of poles	5
Connection type	Screw connection
Degree of protection (IP)	IP66/67/69K

### Material

Housing material	Polyamide
------------------	-----------

Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

**Dimensions**

Length	80.4 mm
Width	34.6 mm
Height	34.6 mm

