


**Datasheet**

Art.No. Z7.284.2627.0

Insulated jumper bar IVBWKN16 - 6

Cross connector, insulated for DIN rail terminal blocks type WKN ..., 6 -pole



Art.No.	Z7.284.2627.0
EAN	4015573157934
Order unit	10 pieces

**Approvals**

**Technical data**

**General**

Colour	Yellow
Type	Cross connector
Modular spacing	15.95 mm
Number of bridged clamps	6
Mounting method	Screwable
Insulated	Yes

**Accessories**

Type	Cross connector
Mounting method	Screwable
Insulated	Yes
Colour	Yellow
Number of bridged clamps	6
Modular spacing	15.95 mm

Drawings

3-polige Ausführung  
3 poles variant

2-30x 05.004.6412.0

2-30x 05.511.0753.0

07.284.20  
32 27.0

2-30x 05.511.0621.0

Das Maß wird bei Änderung besonders geprüft.  
Anzahl ist für 1 Stück.  
Mit 10.000 Stück/Menge sind nur 10.000 Stück möglich.

Teile-Nr. part nr.	Pol- zahl poles	L	l	Typ type
Z7.284.20MM.0	30	355,55	346,55	IVB WKN 16 M-30
Z7.284.22MM.0	2	20,95	11,95	IVB WKN 16-2
Z7.284.23MM.0	3	32,9	23,9	IVB WKN 16-3
Z7.284.24MM.0	4	44,85	35,85	IVB WKN 16-4
Z7.284.25MM.0	5	56,8	47,8	IVB WKN 16-5
Z7.284.26MM.0	6	68,75	59,75	IVB WKN 16-6
Z7.284.27MM.0	7	80,7	71,7	IVB WKN 16-7
Z7.284.28MM.0	8	92,65	83,65	IVB WKN 16-8
Z7.284.29MM.0	9	104,6	95,6	IVB WKN 16-9
Z7.284.30MM.0	10	116,55	107,55	IVB WKN 16-10
Z7.284.31MM.0	11	128,5	119,5	IVB WKN 16-11
Z7.284.32MM.0	12	140,45	131,45	IVB WKN 16-12

MM

27

Katalogteil  
catalogue part

97

spezielle Verpackung  
special packing

Freieleranz nach DIN		CND - Zeichnung, keine masselien Änderungen		1. Verwendung: -		Bl.: 1 von 1	
/	Maßstab	2002	Tag	Nama	Zeichnung Nr.		Index
/	x	Entworfen	06.03.	Freschen	T		Z7.284.2027.0 01K a
/		Begrüßt	-	-			
/		Nenngrö.	-	-	Ersatz für:		
		<b>wieland</b>		<b>VERBINDUNGSSTEG</b> jumper bar			
Elektrische Verbindungen		Typ IVB WKN 16-x		Benennung			
Änderung		03.11.2003/ Ausgabe Datum / Blatt					

A  
1  
2  
3  
4  
5  
6  
7  
8  
9  
10  
11  
12  
13  
14  
15  
16  
17  
18  
19  
20  
M1  
M2  
M3  
L  
G  
i  
1.1  
2.1  
1.1

Z7.284.2027.01K\_a\_CADWZ02 Bauer 03.11.2003 12:35:02 1.000