

Datasheet

Art.No. Z7.409.8856.0

Cover BAS AD DA 16 FS

Protective cover with tether cord without locking levers, without gasket size BG 16



Art.No.	Z7.409.8856.0
EAN	4015573159112
Order unit	10 pieces

Approvals

Technical data

General

Degree of protection (IP)	IP65
Inflammability class of insulation material acc. with UL94	V0
Housing material	Plastic
Surface	Untreated
Colour	Grey
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	16
Interlock	No
Locking mechanism	Double locking levers
Material locking lever	None
Cover attachment clamping	No
With sealing	No
With tether cord	Yes
With loop	Yes
With ring lug	No

Drawings

gez. Ausf. Z7.409.8756.0
 drawn version Z7.409.8756.0

Fangsnur/catch cord

20

13

2

L1

L2

weitere Daten siehe Katalog
 further data see catalog

Teile Nr. part no.	Größe size	L1	L2
Z7.409.8756.0	10	26,5	75,5
Z7.409.8856.0	16	47,0	96,0
Z7.409.8956.0	24	73,5	122,5

Freiheranz nach		CAD - Zeichnung, keine manuellen Änderungen			1. Verwendung: -		Bl.: 1 von 1	
/	Maßstab	Werkstoff und Oberfläche:			2005		Tag	
/	1:1				Entworfen		14.06. Schmitt J.	
/					Geprüft			
/	Vol.	mm ²	Ohm	mm ²	Nenngr.	Ersatz für -		
/		wieland			revos		Benennung	
/		Elektrische Verbindungen			Größe 10-24		SCHUTZDECKEL	
/	Änderung				size 10-24		für Steckverbinder u. Klemmadapter protective cover f. multipole connector and adaptor	

Z7498756001K_4_CAD0205 Schmitt 2005-06-15 10:08:43 1:000