

Datasheet

Art.No. 05.544.1929.8

Male contact D 3,6- 2,5 QMM AG

Male contact, turned Ø 3,6 mm, 2,5 mm², AWG 14, Ag



| | |
|------------|---------------|
| Art.No. | 05.544.1929.8 |
| EAN | 4015573681736 |
| Order unit | 100 pieces |

Approvals

Technical data

General

| | |
|--|---------------|
| Model | Pin |
| Wire strip length | 10 mm |
| Min. conductor cross section flexible wire | 2.5 |
| Max. conductor cross section flexible wire | 2.5 |
| Min. UL/CSA wire diameter flexible wire | 14 AWG |
| Max. UL/CSA wire diameter flexible wire | 14 AWG |
| Mating cycles | 500 |
| Connection type | Crimp |
| Material | Other |
| Massive contact | Yes |
| Contact pin diameter | 3.6 mm |
| Surface | Silver-plated |
| Inflammability class of insulation material acc. with UL94 | Other |
| Contact resistance | 1 mOhm |