

Datasheet

Item No. Z7.268.2027.0

Jumper bar IVB WKF 1,5-20

Cross connector, insulated for DIN rail terminal blocks type WKF..., 20 -pole



Item No.	Z7.268.2027.0
EAN	4015573732056
order unit	10 Piece(s)

Technical data

**Accessories**

Colour	Yellow
Type	Cross connector
Modular spacing	4.2 mm
Number of bridged clamps	20
Mounting method	Pluggable
Insulated	Yes

Drawings

Isolierung  
gelb/  
insulation  
yellow

**Z7.268.0227.0**  
M 1:1

Weitere Daten siehe Katalog  
further data see catalog

Teile-Nr. part-number	Typ type	Polzahl pole	L
Z7.268.0227.0	IVB WKF 1,5- 2	2	7,0
Z7.268.0327.0	IVB WKF 1,5- 3	3	11,2
Z7.268.0427.0	IVB WKF 1,5- 4	4	15,4
Z7.268.0527.0	IVB WKF 1,5- 5	5	19,6
Z7.268.1027.0	IVB WKF 1,5-10	10	40,6
Z7.268.2027.0	IVB WKF 1,5-20	20	82,6

Freitoleranz nach DIN	CAD - Zeichnung, keine manuellen Änderungen	1. Verwendung: -	Bl.: 1 von 1
Maßstab	Werkstoff und Oberfläche:	2004	Tag
5:1		Entworfen	09.11.
		Schmitt	J.
		Gepüßt	-
		Normgepr.	-
<b>wieland</b> Elektrische Verbindungen		Typ IVB WKF 1,5-...	Benennung <b>VERBINDUNGSSTECKER</b> insulated jumper bar
Zeichnung Nr.		Index	
T		Z7.268.0227.0 01K	
Ersatz für: -			

A  
1  
2  
3  
4  
5  
6  
7  
8  
9  
10  
11  
12  
13  
14  
15  
16  
17  
18  
19  
20  
M1  
M2  
M3  
L  
G  
i  
1.1  
12.1  
1.1  
Z72680227001K\_4\_CADWZ8\_Schmitt\_2004-11-09T15:33:52\_1:000