

Datasheet

Item No. Z7.281.7827.0

Insulated jumper bar IVB WK 4/D..- 8

Cross connector, insulated for DIN rail terminal blocks type WK ..., 8-pole



Item No.	Z7.281.7827.0
EAN	4015573156692
order unit	10 Piece(s)

Technical data

Accessories

Colour	Yellow
Type	Cross connector
Modular spacing	5.95 mm
Number of bridged clamps	8
Mounting method	Screwable
Insulated	Yes

Drawings

4-polige Ausführung
4 poles variant

Teile-Nr. part nr.	Pol- zahl poles	L	l	Typ type
Z7.281.72MM.0	2	10,35	5,95	IVB WK4/D...-2
Z7.281.73MM.0	3	16,3	11,9	IVB WK4/D...-3
Z7.281.74MM.0	4	22,25	17,85	IVB WK4/D...-4
Z7.281.75MM.0	5	28,2	23,8	IVB WK4/D...-5
Z7.281.76MM.0	6	34,15	29,75	IVB WK4/D...-6
Z7.281.77MM.0	7	40,1	35,7	IVB WK4/D...-7
Z7.281.78MM.0	8	46,05	41,65	IVB WK4/D...-8
Z7.281.79MM.0	9	52	47,6	IVB WK4/D...-9
Z7.281.80MM.0	10	57,95	53,55	IVB WK4/D...-10
Z7.281.81MM.0	11	63,9	59,5	IVB WK4/D...-11
Z7.281.82MM.0	12	69,85	65,45	IVB WK4/D...-12

MM	
27	Katalogteil catalogue part
97	spezielle Verpackung special packing

Freitoleranz nach DIN CAD-Zeichnung, keine manuellen Änderungen I. Verwendung: - Bl.: 1 von 1

2002	Tag	Name	Zeichnung Nr.	index
Entworfen	08.03.	Treschan	Z7.281.7227.0 01K	
Geprüft				
Normgepr.				

wieland
Elektrische Verbindungen

Typ: IVB WK4/D...
Benennung: VERBINDUNGSSTEG
jumper bar

Z72817227001 CAD04028 treschan 08.03.2002 13:51:29 1.000