

Datasheet

Item No. Z7.283.2527.0

Insulated jumper bar IVBWKN10 - 5

Cross connector, insulated for DIN rail terminal blocks type WKN ..., 5 -pole



Item No.	Z7.283.2527.0
EAN	4015573157309
order unit	10 Piece(s)

Technical data

Accessories

Colour	Yellow
Type	Cross connector
Modular spacing	10 mm
Number of bridged clamps	5
Mounting method	Screwable
Insulated	Yes

Drawings

4-polige Ausführung
4 poles variant

07.283.22 27.0

05.561.42 53.0

8,1

13,4

1,5

2-12x 05.511.0821.0

L

10

2-12x 05.003.2612.0

Teile-Nr. part nr.	Pol- zahl poles	L	l	Typ type
Z7.283.22MM.0	2	17,2	10	IVB WKN 10-2
Z7.283.23MM.0	3	27,2	20	IVB WKN 10-3
Z7.283.24MM.0	4	37,2	30	IVB WKN 10-4
Z7.283.25MM.0	5	47,2	40	IVB WKN 10-5
Z7.283.26MM.0	6	57,2	50	IVB WKN 10-6
Z7.283.27MM.0	7	67,2	60	IVB WKN 10-7
Z7.283.28MM.0	8	77,2	70	IVB WKN 10-8
Z7.283.29MM.0	9	87,2	80	IVB WKN 10-9
Z7.283.30MM.0	10	97,2	90	IVB WKN 10-10
Z7.283.31MM.0	11	107,2	100	IVB WKN 10-11
Z7.283.32MM.0	12	117,2	110	IVB WKN 10-12

MM	
27	Katalogteil catalogue part
97	spezielle Verpackung special packing

Freioleranz nach DIN

CAD - Zeichnung, keine manuellen Änderungen

1. Verwendung: -

Bl.: 1 von 1

Maßstab	2002	Tag	Name	Zeichnung Nr.	Index
/	Entworfen	06.03.	Treschan	Z7.283.2227.0 01K	
/	Gepflegt				
/	Normgepr.			Ersatz für:	

wieland

Elektrische Verbindungen

Typ: IVB WKN 10-..

Benennung: VERBINDUNGSSTEG jumper bar

7283227001 CAD028 treschan 07.03.2002 13:24:30 1000