

Datasheet

Item No. Z7.283.2627.0

Insulated jumper bar IVBWKN10 - 6

Cross connector, insulated for DIN rail terminal blocks type WKN ..., 6 -pole



Item No.	Z7.283.2627.0
EAN	4015573157323
order unit	10 Piece(s)

Technical data

Accessories

Colour	Yellow
Type	Cross connector
Modular spacing	10 mm
Number of bridged clamps	6
Mounting method	Screwable
Insulated	Yes

Drawings

4-polige Ausführung
4 poles variant

07.283.22²²27.0
05.561.42⁴²53.0

2-12x 05.511.0821.0

2-12x 05.003.2612.0

Teile-Nr. part nr.	Pol- zahl poles	L	l	Typ type
Z7.283.22MM.0	2	17,2	10	IVB WKN 10-2
Z7.283.23MM.0	3	27,2	20	IVB WKN 10-3
Z7.283.24MM.0	4	37,2	30	IVB WKN 10-4
Z7.283.25MM.0	5	47,2	40	IVB WKN 10-5
Z7.283.26MM.0	6	57,2	50	IVB WKN 10-6
Z7.283.27MM.0	7	67,2	60	IVB WKN 10-7
Z7.283.28MM.0	8	77,2	70	IVB WKN 10-8
Z7.283.29MM.0	9	87,2	80	IVB WKN 10-9
Z7.283.30MM.0	10	97,2	90	IVB WKN 10-10
Z7.283.31MM.0	11	107,2	100	IVB WKN 10-11
Z7.283.32MM.0	12	117,2	110	IVB WKN 10-12

MM	
27	Katalogteil catalogue part
97	spezielle Verpackung special packing

Freioleranz nach DIN CAD - Zeichnung, keine manuellen Änderungen 1. Verwendung: - Bl.: 1 von 1

Maßstab	2002 Tag Name	Zeichnung Nr.	Index
/	Entworfen 06.03. Treschan	Z7.283.2227.0 01K	
/	Gepf. -		
/	Normgepr. -	Ersatz für:	
/	Typ: IVB WKN	Benennung	
/	10-..	VERBINDUNGSSTEG jumper bar	

Wieland Elektrische Verbindungen

Z7283227001 CAD028 freeschon 07.03.2002 13:24:30 1000