


NOTES: UNLESS OTHERWISE SPECIFIED

1. P/N: XB-2ACOLOR  
 HOUSING: MOLDED NYLON. AVAILABLE IN BLK, RED, YEL.  
 KNOB: MOLDED PLASTIC. AVAILABLE IN BLK, RED, YEL.  
 NEEDLES: TIN PLATED MUSIC WIRE  
 NEEDLE CLUSTER HOUSING: TIN PLATED BRASS  
 CLAMPING SCREW: STAINLESS STEEL.
2. P/N: W-600/COLOR  
 18AWG TINNED COPPER  
 0.144 [3.66] O.D. PVC INSULATION  
 AVAILABLE IN TEN COLORS.
3. PERFORMANCE  
 MAXIMUM CURRENT: 500 MILLIAMPS  
 MAXIMUM VOLTAGE: <33 V AC < 70 V DC  
 MAXIMUM TEMPERATURE: 221°F (105°C)

REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± ± .XXX ±	CONTRACT NO.		<b>E-Z-HOOK</b> DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.	
			APPROVALS	DATE		
		MATERIAL SEE NOTE.	DRAWN	R.L.	10/18	
			APPROVED BY			
		FINISH SEE NOTE.	SIZE	CODE IDENT NO.	DRAWING NO.	REV.
NEXT ASSY	USED ON		B	08505	613XB	
APPLICATION		DO NOT SCALE DRAWING	SCALE	1:1	SHEET 1 OF 1	