

Direct Links

- Cross Reference
- RoHS/LF P/N search
- Document & Drawing search
- Application tooling

Services

- Contact us
- Distributor list
- Pricing request
- Order samples

Literature

- Brochures & catalogs
- Product documentation
- Technical library

8638PSS1505LF

8638PSS1505LF

[Assistant](#) [Add to Favorites](#)



8638PSS1505LF - D-Subminiatures

Power contacts 8638 Socket Solder Bucket 15 A, >200 Cycles

[Email Datasheet](#) [Print Datasheet](#)

FCI Brings You More

- [Contact our sales/technical support](#)
- [Sample request](#)
- € [Price request](#)
- [Check distributor stock](#)

ACTIVE

[Customer Drawing](#)



Electronics division

Download document

Technical Resources

[> RoHS qualification documents](#)

Literature

[> D-Subminiature Brochure](#)

[> Connector Overview Brochure](#)

Application Tooling

[> Asia Pacific Application Tooling](#)

[> Americas Application Tooling](#)

[> Europe Application Tooling](#)

Specifications

General	Dimensional	Electrical	Mechanical	Physical
General				
Contact type			Power	
Gender			Socket	
Product Type			Contact	
Termination Style			Solder Bucket	
Dimensional				
Length (Overall)			22 mm max	
Size (Wire)			14 AWG	
Strip length (Wire)			7 mm	
Diameter A (Inner)			2.1 mm	
Diameter B (outer)			3 mm	
Electrical				
Current rating			15A	
Mechanical				
Durability (Mating cycles)			> 200 Cycles	
Physical				
Plating (Contact)			Gold over Nickel	
Color (Clip)			White	
Plating (Termination)			Matte Tin over Nickel	