


CURRENT RATING 1.5A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)

RATED VOLTAGE : 500 V AC (CONT./CONT)


OPERATING TEMPERATURE : -55°C TO 125°C

CONTACT RESISTANCE 20 MΩ MAX

INSERTION FORCE : 0.75N MAX/CONT

EXTRACTION FORCE : 0.15N MIN/CONT

INSULATION RESISTANCE : 10^4 MΩ MIN



2. THIS PRODUCT IS CSA APPROVED.
THIS PRODUCT IS UL RECOGNIZED.
3. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING :
BSA.201572.001
4. THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

		www.fciconnect.com				tolerance 1DEC ±0.2 1DEC 2DEC ±0.1 2DEC ANGLES ±1° HDKLEN		projection 			
Dr	M.Fret	04-01-00	Product family		MILLIPICS		size	A4		Scale	
Eng			Spec ref							3/1	
Chr			Material				ECN				
Appr											
title MPACS 8+2R RA RCP CONN TYPE E/ UPPER SHIELDED						dwg no BS,C ,202260,021		Rev D			
catalog no			HM2R88PA810F----			CUMSTOMER			sheet 1 of 1		