










FCIconnect.com

Copyright FCI.


PRODUCT NO.
10125836-**-001**



CIRCUIT No.1



20,000	2,000	1,000	4.8	7.5	8.5	6.0	10125836-06-001SP	6
	5,000						10125836-06-001	
40,000	2,000	2,000	5.1	6.1	3.6	3.9	10125836-04-001SP	4
	10,000						10125836-04-001	
40,000	2,000	2,000	3.9	4.9	2.4	2.4	10125836-03-001SP	3
	10,000						10125836-03-001	
INNER BOX (pcs)	INNER BOX (pcs)	POLY BAG (pcs)	D	C	B	A	PRODUCT NO.	CIRCUIT

mat'l. code ---					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family					CODE JP			
ltr	description		ecn no		dr	date		tolerances unless otherwise specified				title							
A	RELEASED				Y.K	2013-12-17		angles linear	0.X ±0.3			PLUG HOUSING FOR 1.2mm PITCH WTB CONNECTOR							
B	REVISED		ELX-J-17235		Y.K	2014-03-19			0.XX ±0.3										
C	REVISED		ELX-J-17474		Y.K	2014-04-16			0°±2° 0.XXX ±0.3										scale 10:1
D	REVISED		ELX-J-22423		Y.K	2015-11-06		dr	Y.KAMEDA		2015-11-09			dwg no		sheet 1 of 1			size
E	REVISED		ELX-J-22440		Y.K	2015-11-09		engr	Y.KAMEDA		2015-11-09			10125836		A3			
								chr	H.SUZUKI		2015-11-09								
								appd	N.SASAME		2015-11-09								
sheet index		revision sheet																Rev. E	

Note
1. Mate with : P/N10125839-****EHLF
2. Applicable terminal : P/N10125837-*****
3. Apply even circuit products. odd circuit products is 0mm.
4. Material : High Temp Thermoplastic, UL94V-0, Black
5. This product meet European Union Directives and other country regulations as described GS-22-008