



DIMENSIONS




TERMINATION



ORDERING INFORMATION

SERIES	8609	3	80	7	1	13	7	6	0	NNLF
ROWS FITTED WITH CONTACTS	Row a	b	c							
NO. OF CONTACTS										80
TYPE OF INSULATOR										7
3 ROW MALE INSULATOR										
METHOD OF MOUNTING										1
STANDARD MOUNTING - STYLE C										
TERMINATION										13
ANGLED SPILL										
OPTIONS										
NO OPTION WITH HARPOONS										7
PERFORMANCE CLASS										
DIN 41612 CLASS 3										4
DIN 41612 CLASS 2										5
DIN 41612 CLASS 1										6
AS PER MIL C 55302 / JSS 50808										8
PITCH PER ROW										
MIXED PITCH										0
LEAD FREE VERSION SPL CONTACTS LOADING										NNLF

CONTACT ARRANGEMENT



1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32
a	X	X	X	X	X	X		X	X	X	X	X	X	X		X	X	X	X	X	X		X	X	X	X	X	X	X		
b	X	X	X	X	X	X	X	X	X	X	X	X	X	X		X	X	X	X	X	X		X	X	X	X	X	X	X		
c	X	X	X	X	X	X		X	X	X	X	X	X	X		X	X	X	X	X	X		X	X	X	X	X	X	X		

☒ STANDARD CONTACT ☐ EMPTY CAVITY ☒ FMLB CONTACT ☒ LMEB CONTACT

GENERAL CHARACTERISTICS & ROHS INFO

REFER DRAWING C-8609-0000A



product family 8609

title DIN STANDARD HEADER ANGLED SPILL DIN 41612 STYLE C

dwg no C-8609-2083 sheet 1 of 1 size A3

type Product Customer Drawing