

- Quick Links
- Cross reference
- RoHS/LF P/N Search
- Industry Standards
- Alphabetical List
- Documentation
- 3D model search
- Customer drawing search
- Multi Selection Search
- Search by category

Start > Search=10127816-18LF* > 10127816-18LF

10127816-18LF
10127816-18LF - Minitek® Pwr4.2 : Minitek® Pwr4.2 Plug Housing, Dual row, 18 positions, Glow Wire Compatible



- Customer drawing
- Product Environmental Compliance Report

ACTIVE

RoHS Compliant

Distributor Stock

[Print Datasheet](#)

FCI Brings You More

- [Contact our sales/technical support](#)
- [Sample request](#)

- Specifications**
- Download document

General Dimensional Electrical Mechanical Physical Approvals / Certifications Other Features

General	
Number of contacts	18
Series	10127816
Dimensional	
Pitch	4.2
Electrical	
Withstanding Voltage	1500 Vac, No breakdown. Current leakage < 5mA
Current rating	UP to 9 Amps
Resistance (Contact)	10 milliohm max.
Resistance (Insulation)	1000M QMin
Voltage rating	600V
Mechanical	
Durability (Mating cycles)	30 Cycles
Insertion force	14.7N max.
Withdrawal Force	1 N min.
Glow Wire Compatible	Yes
Physical	
Color (Housing)	Natural
Material (Housing)	Nylon 66
Temperature (Range)	-40°C to +105°C
Approvals / Certifications	
Approvals / Certifications	UL Approved
UL File Number	ML E467317
Other Features	
Packaging (Type)	PE Bag

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.