

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search


Multi Selection Search

Search by category

Start > Search=10127816-08LF* > 10127816-08LF

10127816-08LF

10127816-08LF - Minitek® Pwr4.2 : Minitek® Pwr4.2 Plug Housing, Dual row, 8 positions, Glow Wire Compatible



ACTIVE

RoHS Compliant

Distributor Stock

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Specifications Download document

General Dimensional Electrical Mechanical Physical Approvals / Certifications Other Features	
General	
Number of contacts	8
Series	10127816
Dimensional	
Pitch	4.2
Electrical	
Withstanding Voltage	1500 Vac, No breakdown. Current leakage < 5mA
Current rating	UP to 9 Amps
Resistance (Contact)	10 milliohm max.
Resistance (Insulation)	1000M QMin
Voltage rating	600V
Mechanical	
Durability (Mating cycles)	30 Cycles
Insertion force	14.7N max.
Withdrawal Force	1 N min.
Glow Wire Compatible	Yes
Physical	
Color (Housing)	Natural
Material (Housing)	Nylon 66
Temperature (Range)	-40°C to +105°C
Approvals / Certifications	
Approvals / Certifications	UL Approved
UL File Number	ML E467317
Other Features	
Packaging (Type)	PE Bag

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.